

# Technical information on self adhesive labeling

## Specification:

- Bottle exterior cleansing with equipment for drying and prevention of condensation
- Capsule mounting for all sizes in common use (shrink or roll-on)
- Shrink and roll-on equipment of the latest type
- 1 front lable (self adhesive)
- 1 back lable (self adhesive)
- 1 award lable or 1 sleeve (self adhesive)

## Important:

- Form, dimensions and material of the lables, capsules and packaging material must be checked by us in advance!
- The machine also can be used in isolation!

## Technical Data:

- Throughput up to 2500 bottles per hour
- Power requirements: 13 KW (32A CEE CEE plug with 25 Amp. fuset)
- Drinking water connection
- Bottle sizes: 0,5 to 1,0 L Other sizes by arrangement
- Bottle height: 170 to 400 mm
- Height of the lable carrier: 140mm max
- Maximum adjustment of the height of the lable from 10 mm to 150 mm measured from the bottom of the bottle

## Dimensions of the lable carrier rolls and the method of spooling

- Diameter of the core (receiver) 76 mm
- Outside diameter of the spool Max: 270 mm
- Internal oder external spooling, Start of the words leading

### Correctly spooled!

Externally spooled, start of words leading  
(internally spooled is also possible)



### Incorrectly spooled !

Externally spooled, end of words leading



## Dimensions of the maschine / trailer

- Length: 4.87 meters (ready to roll) 4.87 meters (operational) The total length in operational state together with the packer is: 10.36 meters.
- Width: 2.03 meters (ready to roll) 2.03 meters (operational)
- Height: about 2.35 meters
- Height of the conveyer belt: about 1.26 meters